



CSI JEWETT

# Sterile Dryer

## Model SSD 2826

### CSI Jewett Dryers - faster drying so you can process more equipment

CSI Jewett SSD 2826 Sterile Dryers offer faster drying in bio-clean air, as recommended by infection control authorities. These dryers can handle large loads, providing quicker drying for more items with any combination of tubes and parts. The air circulation system consists of a pre-filter and a HEPA filter to eliminate the threat of airborne pathogens, such as bacteria and particles from re-contaminating parts while they are being dried. For safety and efficiency, Sterile Dryers should be used in conjunction with a washer disinfectant or other high-level cleaning method.

#### Standard Features

- Heavy Gauge Polished Stainless Steel Construction
- Speeds drying
- Drying temperature fully adjustable to meet drying requirements
- Digital temperature controller (preset at the factory for normal operation) provides accurate and consistent chamber temperatures
- Thermal cutoff
- Automatic timer
- Protects the load while drying
- Provides short-term storage
- HEPA filter is 99.97% efficient in removing all particles larger than 0.3 of a micron
- Recirculating air system provides extra efficiency through reuse of warm air
- Large capacity
- See through doors
- Adjustable shelving provides flexible loading
- Recessed, front mounted heating system controls to prevent accidental contact
- Safety features include built-in thermal protection switch fuses and overload protection for blower motor

#### Optional Inhalation Tube Header

When used in conjunction with CSI Jewett's Inhalation Tube Header, CSI Jewett Sterile Dryers allow for transfer of already mounted tubes directly to the Sterile Dryer. This results in more efficient handling by saving time when not needing to individually remount the tubes. The Tube Mounting Rack from the header can be moved into place in the Sterile Dryer without additional adjustment needed.

---

#### Simply Put, Built to Last

---

#### Additional Options

- Additional options
- Single freestanding or double door pass through
- Single Width - 28" Wide (*Custom sizes available on request*)
- Additional shelving
- External vent attachment


## Utilities

**Electrical (E)** Available single phase or 3 phase electric


Model	Standard Unit Size
2826	27.75" W x 82.75" H x 26" D 705 mm W x 2102 mm H x 660 mm D

Available in single side or pass-through options.


### Representative Drawings




Top View



Front View



Side View



Scientek does not recommend nor imply in any way that the Scientek washer disinfector be used for the terminal decontamination of any regulated medical device. For processing of a specific material or products, follow the manufacturers recommended cleaning techniques and processes.

SSD 2826 Sterile Dryer Sell Sheet\_M1034\_1.00 2021-0318